

OpenLogger Reference Manual



OpenLogger is a wireless data logging and data acquisition device that can be controlled via USB or WiFi. Using a computer or mobile device, signals from circuits and sensors can be acquired, stored, analyzed, visualized, and generated. OpenLogger makes it easy to monitor multiple analog inputs and simultaneously log the data to an SD card, and/or stream over USB or WiFi, all through WaveForms Live.



Features

- Connectivity
 - ATWINC1500 WiFi chip (802.11n)
 - USB 2.0 (High Speed Required)
- Analog Inputs
 - o 8 Channels
 - 16-bit resolution per channel
 - 400 kS/s sample rate
 - 50 kHz of bandwidth at -3dB
 - $\circ \quad 1\ M\Omega \ of \ input \ impedance$
 - ±10 V input voltage range
 - Maximum buffer size of 32640 samples per channel
- Function Generator
 - o 1 Channel
 - Sine, triangle, sawtooth, square and DC outputs
 - 10-bit resolution
 - 2 MS/s sample rate
 - 3 V pk2pk output with ±1.5 V offset
 - o 10 mA output current
 - 25000 sample buffer size
- Logic Analyzer and GPIO
 - 10 Channels multiplexed between the Logic Analyzer and as general purpose IO
 - 3.3V CMOS logic for both the Logic Analyzer and GPIO
 - 7 mA source and 12 mA sink when used as GPIO
 - Logic Analyzer has a sample rate of 10 MS/s
 - Maximum buffer size of 32640 samples per channel for the Logic Analyzer
- Power Supply
 - o 2 Channels
 - ±4 V output voltage
 - o 50 mA per channel
- Other features
 - USB powered device
 - o 4 user LEDs

OpenLogger Pinout



OpenLogger J1 Header Pinout							
Top Row			Bottom Row				
Pinout#	Pin Name	Pin Description	Pinout#	Pin Name	Pin Description		
1+	AI1	Analog Input 1	Ų	AGND1	Analog Ground		
2+	AI2	Analog Input 2	ţ	AGND2	Analog Ground		
3+	AI3	Analog Input 3	Ų	AGND3	Analog Ground		
4+	Al4	Analog Input 4	Ų	AGND4	Analog Ground		
5+	AI5	Analog Input 5	ţ	AGND5	Analog Ground		
6+	AI6	Analog Input 6	ţ	AGND6	Analog Ground		
7+	AI7	Analog Input 7	ţ	AGND7	Analog Ground		
8+	AI8	Analog Input 8	ţ	AGND8	Analog Ground		
5V	5V	5V Supply	\checkmark	GND	Digital Ground		
R	RST	Button Reset	Ρ	PROG	Button Program		
TI	Tin	Reserved	то	Tout	Reserved		
W1	AWG	Function Generator Output	Ŷ	GND	Digital Ground		

OpenLogger J1 Header Pinout								
Top Row			Bottom Row					
Pinout#	Pin Name	Pin Description	Pinout#	Pin Name	Pin Description			
V1	DC1	DC Out 1	Ŷ	GND	Digital Ground			
V2	DC2	DC Out 2	Ŷ	GND	Digital Ground			
DO	DIOO	Digital IO 0	D4	DIO4	Digital IO 4			
D1	DIO1	Digital IO 1	D5	DIO5	Digital IO 5			
D2	DIO2	Digital IO 2	D6	DIO6	Digital IO 6			
D3	DIO3	Digital IO 3	D7	DIO7	Digital IO 7			

Walk Around the Board



Software Support

The Digilent Agent and WaveForms Live are used to configure and communicate with the OpenLogger, as well as for viewing captured data. More information can be found on their respective Resource Centers, linked above, as well as the OpenLogger Resource Center.

Important!

The OpenLogger can only be used with Windows operating systems.

Analog Inputs

Analog inputs provide ways to measure real analog data from external systems. OpenLogger has 8 single-ended analog inputs with their own recommended ground pin. Each input is designed to accept a voltage range of -10 V to +10 V (with protection up to ±30 V and has 16 bits of resolution and a bandwidth of 50 kHz. OpenLogger can then log all data onto the local SD card at 400 kS/s, stream and/or log data over USB at 200 kS/s, or stream and/or log data over WiFi at 10 kS/S.

The analog inputs has the following features:

- 8 Channels
- 16 bits of resolution per channel
- 500 kS/s aggregate input
- 50 kHz bandwidth at -3 dB

Information on how to use the OpenLogger's Analog Inputs can be found in the OpenLogger's Data Logger tutorial.



Function Generator

The OpenLogger has a single channel 2 MS/s, 10-bit function generator. An R2R resistor ladder with 1% resistors is used in place of a DAC.

The function generator supports:

- Sine, triangle, sawtooth, square and DC outputs
- 10-bit resolution
- 1 Hz to 200 kHz frequency
- 3 V pk2pk output with ±1.5 V offset
- 20 mA output current

Information on how to use the OpenLogger's Function Generator can be found in the OpenLogger's Function Generator tutorial.



Digital I/O

Digital I/O provide generic inputs and outputs to detect and provide ways to detect and provide high and low logic states. The OpenLogger has 8 user IO pins that are available for general use.

Information on how to use the OpenLogger's Digital I/O can be found in the OpenLogger's Digital I/O tutorial.



DC Power Supplies

OpenLogger has two DC outputs that are driven by their own PWM output with a single PWM line for the DC offset. A gain circuit is implmented on the OpenLogger to provide a voltage range of -4 V to 4 V for each channel. A feedback circuit is also present to allow for calibration of the DC output.

- 2 channels
- ±4 V
- 50 mA per channel

Information on how to use the OpenLogger's Power Supplies can be found in the OpenLogger's Power Supplies tutorial.



Troubleshooting

LED Indicators

The LEDs on the OpenLogger are used to indicate the current status of the OpenLogger hardware as follows:

- Orange On Device is booting and not ready to use.
- Green Flashing Device is booted and ready to use, but not logging.
- Green Solid Device is logging to the RAM buffer and streaming is currently available.
- Green and Orange Solid Device is both logging and streaming.
- Green Solid and Orange Flashing Device is streaming to the RAM buffer, but logging to the SD card or through Wifi has stopped
 - \circ For the SD card, this usually indicates there is no more space on the SD card
- Red Solid One of the internal buffers was overrun
 - Filling the SD card does not cause an overrun condition
- Red Flashing Warning that the device is falling behind with keeping the buffers cleared
- Blue Solid Reserved for WiFi (not yet implemented)
- Red blinking and Orange Solid Device firmware updating
- All user LEDs Solid An error has occurred. Reboot the OpenLogger and report the error on the Digilent Forum.



